

O & M

Beha TSH 80

Drying rack

BEHA



Description of the drying rack TSH 80

Drying rack TSH 80 provides a simple and quick drying of footwear and clothes. It can also be used for drying towels. The Drying Rack has an effect of 80W and is 90 cm long. Wall mounted and can be clipped up when not in use.

The packaging is recyclable and should be disposed of in paper containers for cardboard.

Electrical connection and use

Before connecting, please ensure that the voltage is 220-240V AC 50Hz. The product should be connected to the electrical socket in the room where it is intended to be used. Do not connect the drying rack with an extension cable as this may cause a fire hazard.

Care and Maintenance

Turned the switch off. Remove the cord from the socket by gripping the plug and gently pull it out of the wall socket. Make sure the product is cooled down before cleaning. Clean the outside with a damp cloth. Never use abrasive cleaners or submerge the drying rack in water or other liquids.

Other information

Defective product must be delivered to a collection point for electrical waste. The drying rack must not be repaired, dismantled, or modified.

Dimension

Name	Effect	Height mm	Length mm	Depth mm	Vare no.	El.no.	Nobb no.	GTIN
TSH 80	80W	65	900	270	21758060	54 498 19	48661506	7026572175802



Contact information: Email: info@scandinaviantrading.co.uk Tel: 01932 645050
Unit 2 Glen Court, Canada Road, Byfleet, KT14 7JL